# **Product data sheet**

Specification





# Spacial SF enclosure with mounting plate - assembled - 1200x600x400 mm

NSYSF12640P

Product availability: Non-Stock - Not normally stocked in distribution facility

Price\*: 1,199.68 USD

## Main

Range	Spacial
Extended Range	Spacial SF
Application	Multi-purpose
Product Or Component Type	Suitable enclosure
Enclosure Nominal Height	47.24 in (1200 mm)
Enclosure Nominal Width	23.62 in (600 mm)
Enclosure Nominal Depth	15.75 in (400 mm)
Enclosure Mounting	Floor-standing
Device Composition	2 sliding rails 4 mounting plate bracket 1 structure 1 door 1 locking system with handle door 1 rear panel 1 roof 1 mounting plate

## Complementary

Structure Type	Formed from a single section Vertical uprights joined with top and bottom frames Panels and doors built into the structure Perforated structure with a pitch of 25 mm
Door Opening Side	Reversible 120 °)
Door Type	Solid front
Mounting Plate Description	Plain
Type Of Gland Plate	Without gland plate
Lock Type	4 points lock, handle with 5 mm double bar insert front door
Number Of Doors	Front 1
Accessibility For Operation	Front Sides of enclosure Rear
Removable Parts	Door by screws hinge Mounting plate by screws mounting plate bracket Rear panel by screws Roof by screws Mounting plate bracket by screws Sliding rail by screws

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Material	Frame galvanised steel Uprights galvanised steel Door sheet steel Panels sheet steel Hinge zamak
Surface Finish	Handle polyamide 6 with 30 % fibre glass epoxy-polyester powder
Color	Enclosure Gray RAL 7035) Handle Black RAL 9005)
Net Weight	169.47 lb(US) (76.871 kg)

## **Environment**

Standards	IEC 62208
Nema Degree Of Protection	NEMA 3R/12
Ip Degree Of Protection	IP55 IEC 60529
Ik Degree Of Protection	IK10 IEC 62262

## Ordering and shipping details

Category	US10ES180035
Discount Schedule	0ES1
Gtin	3606485117386
Returnability	No
Country Of Origin	ES

## **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	19.29 in (49.0 cm)
Package 1 Width	25.39 in (64.5 cm)
Package 1 Length	52.36 in (133.0 cm)
Package 1 Weight	156.53 lb(US) (71.0 kg)
Unit Type Of Package 2	PAL
Number Of Units In Package 2	2
Package 2 Height	52.36 in (133.0 cm)
Package 2 Width	25.59 in (65.0 cm)
Package 2 Length	38.58 in (98.0 cm)
Package 2 Weight	313.06 lb(US) (142.0 kg)

## **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

## Well-being performance



Mercury Free



Rohs Exemption Information

Yes

### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration  Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations