


Product availability : Non-Stock - Not normally stocked in distribution facility



Price\* : 2,117.73 USD



### Main

Range	Spacial
Extended range	Spacial SF-E
Application	Electronic application
Product or component type	Suitable enclosure
Enclosure nominal height	47.24 in (1200 mm)
Enclosure nominal width	23.62 in (600 mm)
Enclosure nominal depth	23.62 in (600 mm)
Enclosure mounting	Floor-standing
Device composition	1 roof 1 structure 1 locking system with handle door 2 door front and rear 2 side panels

### Complementary

Structure type	Formed from a single section Vertical uprights joined with top and bottom frames Panels and doors built into the structure Perforated structure with a pitch of 25 mm
Door type	Plain on front Glazed on rear
Number of doors	2 on front and rear
Door opening side	Reversible 120 °
Lock type	4 points lock, handle with 5 mm double bar insert on front and rear doors
Mounting plate description	Without mounting plate
Type of gland plate	Without gland plate
Accessibility for operation	Front Rear Sides of enclosure

Removable parts	Roof fixed by screws Door fixed by screws hinge Side panel fixed by screws
Material	Galvanised steel frame Galvanised steel uprights Polyamide 6 with 30 % fibre glass handle Sheet steel door Sheet steel panels Zamak hinge
Surface finish	Epoxy-polyester powder
Colour	Enclosure: grey RAL 7035 Handle: black RAL 9005

## Environment

Standards	IEC 62208
IP degree of protection	IP55 conforming to IEC 60529
IK degree of protection	IK08 of transparent door conforming to IEC 62262 IK10 of plain door conforming to IEC 62262

## Ordering and shipping details

Category	80035 - ENCLOSURE SYSTEMS FLOOR MOUNT
Discount Schedule	ES1
GTIN	003606485127323
Nbr. of units in pkg.	1
Package weight(Lbs)	2.2000000000000002
Returnability	N
Country of origin	ES

## Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0852 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations

## Contractual warranty

Warranty period	18 months
-----------------	-----------