

NSYSF181050P

Spacial SF enclosure with mounting plate -
assembled - 1800x1000x500 mm

Product availability : Non-Stock - Not normally stocked in distribution facility



Price* : 1,762.04 USD



Main

| | |
|---------------------------|---|
| Range | Spacial |
| Extended range | Spacial SF |
| Application | Multi-purpose |
| Product or component type | Suitable enclosure |
| Enclosure nominal height | 70.87 in (1800 mm) |
| Enclosure nominal width | 39.37 in (1000 mm) |
| Enclosure nominal depth | 19.69 in (500 mm) |
| Enclosure mounting | Floor-standing |
| Device composition | 1 door 1 mounting plate 1 rear panel 1 roof 1 structure 1 locking system with handle door 2 sliding rails 4 mounting plate bracket |

Complementary

| | |
|-----------------------------|--|
| Structure type | Formed from a single section Vertical uprights joined with top and bottom frames Panels and doors built into the structure Perforated structure with a pitch of 25 mm |
| Door type | Plain on front |
| Number of doors | 1 on front |
| Door opening side | Reversible 120 ° |
| Lock type | 4 points lock, handle with 5 mm double bar insert on front door |
| Mounting plate description | Plain |
| Type of gland plate | Without gland plate |
| Accessibility for operation | Front |

| | |
|-----------------|---|
| | Rear Sides of enclosure |
| Removable parts | Rear panel fixed by screws Roof fixed by screws Door fixed by screws hinge Mounting plate bracket fixed by screws Sliding rail fixed by screws Mounting plate fixed by screws mounting plate bracket |
| Material | Galvanised steel frame Galvanised steel uprights Polyamide 6 with 30 % fibre glass handle Sheet steel door Sheet steel panels Zamak hinge |
| Surface finish | Epoxy-polyester powder |
| Colour | Enclosure: grey RAL 7035 Handle: black RAL 9005 |

Environment

| | |
|-------------------------|------------------------------|
| Standards | IEC 62208 |
| IP degree of protection | IP55 conforming to IEC 60529 |
| IK degree of protection | IK10 conforming to IEC 62262 |

Ordering and shipping details

| | |
|-----------------------|---------------------------------------|
| Category | 80035 - ENCLOSURE SYSTEMS FLOOR MOUNT |
| Discount Schedule | ES1 |
| GTIN | 00785901921295 |
| Nbr. of units in pkg. | 1 |
| Package weight(Lbs) | 336.07999999999998 |
| Returnability | N |
| Country of origin | ES |

Offer Sustainability

| | |
|----------------------------------|---|
| Sustainable offer status | Green Premium product |
| RoHS (date code: YYWW) | Compliant - since 0940 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity |
| REACH | Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold |
| Product environmental profile | Available |
| Product end of life instructions | Need no specific recycling operations |

Contractual warranty

| | |
|-----------------|-----------|
| Warranty period | 18 months |
|-----------------|-----------|