

Product availability : Non-Stock - Not normally stocked in distribution facility



Price* : 3,315.74 USD



Main

Range	Spacial
Extended range	Spacial SF
Application	PC application
Product or component type	Suitable enclosure
Enclosure nominal height	70.87 in (1800 mm)
Enclosure nominal width	23.62 in (600 mm)
Enclosure nominal depth	23.62 in (600 mm)
Enclosure mounting	Floor-standing
Product specific application	Protecting computer equipment
Device composition	1 cable gland plate 1 roof 1 structure 2 side panels 1 partial door for keyboard 1 partial door for PC screen 1 partial door for printer support 1 rear door 1 partial door for CPU

Complementary

Structure type	Formed from a single section Vertical uprights joined with top and bottom frames Panels and doors built into the structure Perforated structure with a pitch of 25 mm
Door type	Plain partial on front Glazed partial on front Plain on rear Hinged plain partial on front
Number of doors	1 on rear 4 on front

Door opening side	Reversible 120 °
Lock type	Flat escutcheon lock, 5 mm double bar on rear door Escutcheon lock, 3 mm double bar on front partial doors
Mounting plate description	Without mounting plate
Type of gland plate	Standard
Cable entry	1 entry
Number of compartments	4
Accessibility for operation	Front Rear Sides of enclosure
Removable parts	Door fixed by screws hinge Roof fixed by screws internally Side panel fixed by screws internally
Material	Galvanised steel frame Galvanised steel uprights Sheet steel door Sheet steel panels Zamak hinge Polyamide 6 with 30 % fibre glass escutcheon
Surface finish	Epoxy-polyester powder
Colour	Enclosure: grey RAL 7035 Handle: black RAL 9005

Environment

Standards	IEC 62208
IP degree of protection	IP55 without hinged keyboard IP40 with hinged keyboard conforming to IEC 60529
IK degree of protection	IK08 of transparent door conforming to IEC 62262 IK10 of plain door conforming to IEC 62262

Ordering and shipping details

Category	80035 - ENCLOSURE SYSTEMS FLOOR MOUNT
Discount Schedule	ES1
GTIN	003606485118765
Nbr. of units in pkg.	1
Package weight(Lbs)	233.20000000000002
Returnability	N
Country of origin	FR

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0940 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------