Product data sheet

Specifications





Spacial SF PC rack enclosure - assembled - 1800x600x600 mm

NSYSF18660PC

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 3,315.74 USD

Main

Range	Spacial
Extended Range	Spacial SF
Application	PC application
Product Or Component Type	Suitable enclosure
Enclosure Nominal Height	70.87 in (1800 mm)
Enclosure Nominal Width	23.62 in (600 mm)
Enclosure Nominal Depth	23.62 in (600 mm)
Enclosure Mounting	Floor-standing
Product Specific Application	Protecting computer equipment
Device Composition	1 structure 1 roof 2 side panels 1 cable gland plate 1 partial door for keyboard 1 partial door for PC screen 1 partial door for printer support 1 rear door 1 partial door for CPU

Complementary

Structure Type	Panels and doors built into the structure Formed from a single section Perforated structure with a pitch of 25 mm Vertical uprights joined with top and bottom frames
Door Opening Side	Reversible 120 °)
Door Type	Plain partial front Glazed partial front Solid rear Hinged plain partial front
Mounting Plate Description	Without mounting plate
Type Of Gland Plate	Standard
Cable Entry	1 entry
Number Of Compartiments	4
Lock Type	Flat escutcheon lock, 5 mm double bar rear door Escutcheon lock, 3 mm double bar front partial doors
Number Of Doors	Front 4 Rear 1
Accessibility For Operation	Sides of enclosure Rear Front

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Removable Parts	Roof by screws internally Side panel by screws internally Door by screws hinge
Material	Frame galvanised steel Uprights galvanised steel Door sheet steel Panels sheet steel Hinge zamak Escutcheon polyamide 6 with 30 % fibre glass
Surface Finish	epoxy-polyester powder
Color	Enclosure Gray RAL 7035) Handle Black RAL 9005)

Environment

Standards	IEC 62208
Nema Degree Of Protection	NEMA 3R/12
Ip Degree Of Protection	IP40 IEC 60529 with hinged keyboard) IP55 without hinged keyboard)
Ik Degree Of Protection	IK08 IEC 62262 of transparent door) IK10 IEC 62262 of plain door)

Ordering and shipping details

Category	US10ES180035
Discount Schedule	0ES1
Gtin	3606485118765
Returnability	No
Country Of Origin	FR

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	25.59 in (65.0 cm)
Package 1 Width	27.17 in (69.0 cm)
Package 1 Length	75.98 in (193.0 cm)
Package 1 Weight	231.49 lb(US) (105.0 kg)

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations