Product data sheet

Specification





Spacial SF enclosure with mounting plate - assembled - 2000x600x400 mm

NSYSF20640P

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 1,650.11 USD

Main

| Range | Spacial |
|--------------------------------|------------------------------------------------------------------------------------------------------------------------------------|
| Extended Range | Spacial SF |
| Application | Multi-purpose |
| Product Or Component Type | Suitable enclosure |
| Enclosure Nominal Height | 78.74 in (2000 mm) |
| Enclosure Nominal Width | 23.62 in (600 mm) |
| Enclosure Nominal Depth | 15.75 in (400 mm) |
| Enclosure Mounting | Floor-standing |
| Device Composition | 2 sliding rails 4 mounting plate bracket 1 structure 1 door 1 locking system with handle door 1 rear panel 1 roof 1 mounting plate |

Complementary

| Structure Type | Formed from a single section Panels and doors built into the structure Perforated structure with a pitch of 25 mm Vertical uprights joined with top and bottom frames |
|-----------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Door Opening Side | Reversible 120 °) |
| Door Type | Solid front |
| Mounting Plate Description | Plain |
| Type Of Gland Plate | Without gland plate |
| Lock Type | 4 points lock, handle with 5 mm double bar insert front door |
| Number Of Doors | Front 1 |
| Accessibility For Operation | Sides of enclosure Rear Front |
| Removable Parts | Door by screws hinge Mounting plate by screws mounting plate bracket Rear panel by screws Roof by screws Mounting plate bracket by screws Sliding rail by screws |

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.



| Material | Frame galvanised steel |
|----------------|------------------------------------------|
| | Uprights galvanised steel |
| | Door sheet steel |
| | Panels sheet steel |
| | Hinge zamak |
| | Handle polyamide 6 with 30 % fibre glass |
| Surface Finish | epoxy-polyester powder |
| Color | Enclosure Gray RAL 7035) |
| | Handle Black RAL 9005) |
| Net Weight | 225.61 lb(US) (102.334 kg) |

Environment

| Standards | IEC 62208 |
|---------------------------|----------------|
| Nema Degree Of Protection | NEMA 3R/12 |
| Ip Degree Of Protection | IP55 IEC 60529 |
| Ik Degree Of Protection | IK10 IEC 62262 |

Ordering and shipping details

| Category | US10ES180035 |
|-------------------|---------------|
| Discount Schedule | 0ES1 |
| Gtin | 3606485117638 |
| Returnability | No |
| Country Of Origin | ES |

Packing Units

| Unit Type Of Package 1 | PCE |
|------------------------------|--------------------------|
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 19.29 in (49.0 cm) |
| Package 1 Width | 25.39 in (64.5 cm) |
| Package 1 Length | 83.86 in (213.0 cm) |
| Package 1 Weight | 227.08 lb(US) (103.0 kg) |
| Unit Type Of Package 2 | PAL |
| Number Of Units In Package 2 | 2 |
| Package 2 Height | 83.86 in (213.0 cm) |
| Package 2 Width | 25.59 in (65.0 cm) |
| Package 2 Length | 38.58 in (98.0 cm) |
| Package 2 Weight | 454.15 lb(US) (206.0 kg) |

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

| Reach Regulation | REACh Declaration |
|--------------------------|------------------------------------------------------------------------------------------------------|
| Eu Rohs Directive | Pro-active compliance (Product out of EU RoHS legal scope) |
| China Rohs Regulation | China RoHS declaration Product out of China RoHS scope. Substance declaration for your information. |
| Environmental Disclosure | Product Environmental Profile |
| Circularity Profile | No need of specific recycling operations |