Product data sheet

Specifications





Spacial SF bottom and top frame - 300x305 mm

NSYSFC35



Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 123.40 USD

Main

Range	Spacial
Accessory / Separate Part Category	Enclosure accessory
Application	Multi-purpose
Product Or Component Type	Framework kit
For Enclosure Nominal Dimensions	- H: 78.74 in (2000 mm) W: 11.81 in (300 mm) D: 19.69 in (500 mm)
Mounting Location	Bottom of vertical uprights Top of vertical uprights
Range Compatibility	Spacial rear panel Spacial side panel Spacial vertical upright
Device Composition	1 bottom frame 1 roof 1 top frame
Quantity Per Set	Set of 1

Complementary

Material	steel
Color	Gray RAL 7035)
Surface Finish	Epoxy-polyester powder
Fixing Mode	By screws - each corner of enclosure
Height	4.33 in (110 mm)
Width	11.81 in (300 mm)
Depth	External 19.69 in (500 mm)

Ordering and shipping details

Category	US10ES180035
Discount Schedule	0ES1
Gtin	3606485118888
Returnability	No
Country Of Origin	ES

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Package 1 Height	5.91 in (15.0 cm)
Package 1 Width	12.99 in (33.0 cm)
Package 1 Length	20.87 in (53.0 cm)
Package 1 Weight	29.32 lb(US) (13.3 kg)

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations