

Product availability : Non-Stock - Not normally stocked in distribution facility



Price\*\* : 1,132.86 USD



### Main

Range	Spacial
Product name	Spacial SM
Product or component type	Compact enclosure
Application	Multi-purpose
Installation accessory type	Floor-standing
Device composition	1 body 2 door 1 cable gland plate 1 locking system with handle door 1 blocking system left door 4 mounting plate bracket
Removable parts	Door by screws hinge Mounting plate bracket by screws
Enclosure nominal height	47.24 in (1200 mm)
Enclosure nominal width	39.37 in (1000 mm)
Enclosure nominal depth	11.81 in (300 mm)

### Complementary

Number of doors	Front 2
Door opening side	Left 120 °) Right 120 °)
Door type	Plain
Lock type	4 points lock, handle with 5 mm double bar insert
Body type	Single piece body with welded rear panel Front part forming a rigid frame with welded corners
Mounting plate description	Without mounting plate
Type of gland plate	Standard
Cable entry	1 entry

Material	Body sheet steel Door sheet steel Hinge zamak
Surface finish	epoxy-polyester powder
Color	Enclosure grey RAL 7035) Handle black RAL 9005)
Accessibility for operation	Front

## Environment

Standards	IEC 62208
Product certifications	DNV BV UL
IP degree of protection	IP55 IEC 60529
IK degree of protection	IK10 IEC 62262

## Ordering and shipping details

Category	80035 - ENCLOSURE SYSTEMS FLOOR MOUNT
Discount Schedule	ES1
GTIN	03606485120478
Package weight(Lbs)	60.37 kg (133.1 lb(US))
Returnability	No
Country of origin	ES

## Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: Cancer and Reproductive Harm - <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Not applicable, out of EU RoHS legal scope
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations

## Contractual warranty

Warranty	18 months
----------	-----------