



Price** : 1,453.01 USD



Main

Range	Spacial
Product name	Spacial SM
Product or component type	Compact enclosure
Application	Multi-purpose
Installation accessory type	Floor-standing
Device composition	1 body 2 door 1 cable gland plate 1 locking system with handle door 1 blocking system left door 4 mounting plate bracket 1 mounting plate
Removable parts	Door by screws hinge Mounting plate by screws mounting plate bracket Mounting plate bracket by screws
Enclosure nominal height	55.12 in (1400 mm)
Enclosure nominal width	47.24 in (1200 mm)
Enclosure nominal depth	15.75 in (400 mm)

Complementary

Number of doors	Front 2
Door opening side	Left 120 °) Right 120 °)
Door type	Plain
Lock type	4 points lock, handle with 5 mm double bar insert
Body type	Single piece body with welded rear panel Front part forming a rigid frame with welded corners
Mounting plate description	Plain
Type of gland plate	Standard

Cable entry	1 entry
Material	Mounting plate galvanised steel Body sheet steel Door sheet steel Hinge zamak
Surface finish	epoxy-polyester powder
Color	Enclosure grey RAL 7035) Handle black RAL 9005)
Accessibility for operation	Front

Environment

Standards	IEC 62208
Product certifications	UL DNV BV
IP degree of protection	IP55 IEC 60529
IK degree of protection	IK10 IEC 62262

Ordering and shipping details

Category	80035 - ENCLOSURE SYSTEMS FLOOR MOUNT
Discount Schedule	ES1
GTIN	00785901929161
Package weight(Lbs)	118.75 kg (261.8 lb(US))
Returnability	No
Country of origin	ES

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals which are known to the State of California to cause Carcinogen & Reproductive harm. For more information go to www.p65warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Not applicable, out of EU RoHS legal scope
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations

Contractual warranty

Warranty	18 months
----------	-----------