Product data sheet

Specifications





Spacial SM compact enclosure with glazed door - 1800x800x400 mm

NSYSM18840T

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 1,738.90 USD

Main

Range	Spacial
Product Name	Spacial SM
Product Or Component Type	Compact enclosure
Application	Multi-purpose
Installation Accessory Type	Floor-standing
Device Composition	body cable gland plate locking system with handle door mounting plate bracket door
Removable Parts	Door by screws hinge Mounting plate bracket by screws
Enclosure Nominal Height	70.87 in (1800 mm)
Enclosure Nominal Width	31.50 in (800 mm)
Enclosure Nominal Depth	15.75 in (400 mm)

Complementary

Number Of Doors	Front 1
Door Opening Side	Reversible 120 °)
Door Type	Glass
Lock Type	4 points lock, handle with 5 mm double bar insert
Body Type	Single piece body with welded rear panel Front part forming a rigid frame with welded corners
Mounting Plate Description	Without mounting plate
Type Of Gland Plate	Standard
Cable Entry	1 entry
Material	Door Securit glass Body sheet steel Door sheet steel Hinge zamak
Surface Finish	epoxy-polyester powder
Color	Enclosure Gray RAL 7035) Handle Black RAL 9005)
Accessibility For Operation	Front
Net Weight	207.23 lb(US) (94 kg)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Environment

Standards	IEC 62208
Product Certifications	UL DNV BV
Ik Degree Of Protection	IK08 IEC 62262
Ip Degree Of Protection	IP55 IEC 60529

Ordering and shipping details

Category	US10ES180035
Discount Schedule	0ES1
Gtin	3606485120973
Returnability	No
Country Of Origin	ES

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	75.98 in (193.0 cm)
Package 1 Width	33.27 in (84.5 cm)
Package 1 Length	19.29 in (49.0 cm)
Package 1 Weight	207.23 lb(US) (94.0 kg)

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations