

# NSYSMX181640

SMX 304L stainless monobloc enclosure,  
H1800xW1600xD400mm, Scotch Brite® finish.

Product availability : Non-Stock - Not normally stocked in distribution facility



Price\*\* : 7,585.16 USD



## Main

Range	Spacial
Product name	Spacial SMX
Enclosure type	Multi-purpose
Category	Compact enclosure
Nominal height	70.87 in (1800 mm)
Nominal width	62.99 in (1600 mm)
Nominal depth	15.75 in (400 mm)
Product installation	Floor-standing
Device composition	1 body 2 door 1 cable gland plate 1 locking system with handle door 4 mounting plate bracket

## Complementary

Body type	Single piece body folded and welded
Door type	Plain
Number of doors	Front face 2
Door opening side	Reversible 120 °)
Lock type	3 points lock, handle with 5 mm double-bar insert
Mounting plate description	Without mounting plate
Type of gland plate	Plain
Accessibility for operation	Front
Removable parts	Door by hinges Mounting plate bracket by screws Cable gland plate by clips
Material	Body and door stainless steel 304L Handle zamak

	Hinge stainless steel
Surface finish	Enclosure Scotch-Brite® brushed Handle painted
Thickness	0.06 in (1.5 mm)
Net weight	335.10 lb(US) (152 kg)

## Environment

Standards	IEC 62208
Product certifications	UL 508 CAN/CSA 22
IP degree of protection	IP55 IEC 60529
IK degree of protection	IK10 IEC 62262
Environmental characteristic	Corrosive Specific hygiene

## Ordering and shipping details

Category	80035 - ENCLOSURE SYSTEMS FLOOR MOUNT
Discount Schedule	ES1
GTIN	03606480155772
Package weight(Lbs)	151.68 kg (334.4 lb(US))
Returnability	No
Country of origin	BG

## Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals which are known to the State of California to cause Carcinogen & Reproductive harm. For more information go to <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a>
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Not applicable, out of EU RoHS legal scope
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations

## Contractual warranty

Warranty	18 months
----------	-----------