

# Product data sheet

Specifications



SMX 316L stainless monobloc enclosure,  
H1800xW800xD400mm, Scotch Brite® finish.

NSYSMX18840H

Product availability: Non-Stock - Not normally stocked in distribution facility

Price\*: 5,844.84 USD

## Main

Range	Spacial
Product Name	Spacial SMX
Enclosure Type	Multi-purpose
Category	Compact enclosure
Nominal Height	70.87 in (1800 mm)
Nominal Width	31.50 in (800 mm)
Nominal Depth	15.75 in (400 mm)
Product Installation	Floor-standing
Device Composition	1 body 1 cable gland plate 1 locking system with handle door 4 mounting plate bracket 1 door

## Complementary

Body Type	Single piece body folded and welded
Door Type	Solid
Door Opening Side	Reversible 120 °)
Number Of Doors	Front face 1
Lock Type	3 points lock, handle with 5 mm double-bar insert
Type Of Gland Plate	Plain
Accessibility For Operation	Front
Mounting Plate Description	Without mounting plate
Material	Handle zamak Hinge stainless steel Body and door stainless steel 316L
Removable Parts	Door by hinges Mounting plate bracket by screws Cable gland plate by clips
Surface Finish	Enclosure Scotch-Brite® brushed Handle painted
Net Weight	216.05 lb(US) (98 kg)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

## Environment

Standards	IEC 62208
Ip Degree Of Protection	IP66 IEC 60529
Ik Degree Of Protection	IK10 IEC 62262
Product Certifications	UL 508 CAN/CSA 22
Environmental Characteristic	Corrosive Specific hygiene

## Ordering and shipping details

Category	US10ES180035
Discount Schedule	0ES1
Gtin	3606480155833
Returnability	No
Country Of Origin	BG

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	18.90 in (48.0 cm)
Package 1 Width	33.46 in (85.0 cm)
Package 1 Length	75.98 in (193.0 cm)
Package 1 Weight	220.46 lb(US) (100.0 kg)

## Contractual warranty

Warranty	18 months
----------	-----------

Sustainability



**Green Premium™ label** is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

 Mercury Free

 RoHS Exemption Information   [Yes](#)

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations