

# Product data sheet

Specifications



PC box IP66 IK08 RAL7035  
Int.H80W80D65 Ext.H89W89D51  
opaque PC cover H10

NSYTBP885

Product availability: Non-Stock - Not normally stocked in distribution facility

**Price\*: 15.05 USD**

## Main

Range	Thalassa
Product Name	Thalassa TBP
Device Application	Multi-purpose
Category	Industrial box
Height	3.50 in (89 mm)
Width	3.50 in (89 mm)
Depth	2.13 in (54 mm)
Internal Height	3.15 in (80 mm)
Internal Width	3.15 in (80 mm)
Internal Depth	1.85 in (47 mm)
Enclosure Mounting	Wall mounted
Device Composition	1 body 1 cover 4 cover screw
Quantity Per Set	Set of 5
Body Type	One piece moulded
Type Of Front Cover	Low plain cover
Cover Fixing	Metal screws
Lock Type	Captive screw flat outside sealed area
Removable Parts	Cover by captive screws

## Complementary

Material	polycarbonate
Color	Gray RAL 7035)
Standards	UL 508 A IEC 62208
Product Certifications	TÜV UL
Electrical Insulation Class	Class II
Mounting Location	Outdoor (with canopy or shelter and anticondensation valve)
Net Weight	0.24 lb(US) (0.108 kg)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

## Environment

Ip Degree Of Protection	IP66 conforming to NEMA 4.4X
Ik Degree Of Protection	IK08 conforming to IEC 62262
Fire Resistance	1760 °F (960 °C)
Ambient Air Temperature For Storage	5...140 °F (-15...60 °C)
Operating Temperature	-13...176 °F (-25...80 °C)

## Ordering and shipping details

Category	US10ES180033
Discount Schedule	0ES1
Gtin	3606480165597
Returnability	No
Country Of Origin	HU

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.01 in (5.1 cm)
Package 1 Width	3.50 in (8.9 cm)
Package 1 Length	3.50 in (8.9 cm)
Package 1 Weight	3.81 oz (108.0 g)
Unit Type Of Package 2	CAR
Number Of Units In Package 2	160
Package 2 Height	16.14 in (41.0 cm)
Package 2 Width	23.62 in (60.0 cm)
Package 2 Length	62.99 in (160.0 cm)
Package 2 Weight	41.14 lb(US) (18.66 kg)
Unit Type Of Package 3	P12
Number Of Units In Package 3	1920
Package 3 Height	47.24 in (120 cm)
Package 3 Width	31.50 in (80 cm)
Package 3 Length	53.54 in (136 cm)
Package 3 Weight	482.81 lb(US) (219 kg)

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

## Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information Yes

## Certifications & Standards

**Reach Regulation**

[REACH Declaration](#)

**Eu Rohs Directive**

Pro-active compliance (Product out of EU RoHS legal scope)

[EU RoHS Declaration](#)

**China Rohs Regulation**

[China RoHS declaration](#)

Pro-active China RoHS declaration (out of China RoHS legal scope)

**Environmental Disclosure**

[Product Environmental Profile](#)

**Circularity Profile**

[End of Life Information](#)