

Product data sheet

Specifications



PanelSet S3D flexicable gland plate with membrane pearcable 428 x 63 mm

NSYTLGME

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 149.45 USD

Main

Range	PanelSeT
Product Or Component Type	Flexicable gland plate
Accessory / Separate Part Category	Cable management accessory
Application	Multi-purpose
Range Compatibility	PanelSeT PanelSeT S3D
Mounting Location	Enclosure bottom
Cable Gland Type	Pierceable by screwdriver
Type Of Gland Plate	Membrane
Cable Outer Diameter	0.39...1.02 in (10...26 mm)
Cable Entry	Without
Device Composition	1 plate membrane
Quantity Per Set	Set of 1
Material	Plate steel Membrane HCE (heat curable elastomer)

Complementary

Color	Plate Gray RAL 7035)
Surface Finish	Epoxy-polyester powder
Height	1.18 in (30 mm)
Width	19.49 in (495 mm) Real 20.08 in (510 mm)
Depth	8.66 in (220 mm)
Net Weight	2.77 lb(US) (1.258 kg)
Thickness	0.06 in (1.5 mm)
Number Of Cut-Out	Undrilled
Cut-Out Dimensions	428 x 63 mm

Ordering and shipping details

Category	US10ES180036
Discount Schedule	0ES1

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Gtin	3606480467677
Returnability	No
Country Of Origin	SK

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.18 in (3.0 cm)
Package 1 Width	8.86 in (22.5 cm)
Package 1 Length	20.08 in (51.0 cm)
Package 1 Weight	2.77 lb(US) (1.258 kg)
Unit Type Of Package 2	PAM
Number Of Units In Package 2	40
Package 2 Height	19.69 in (50.0 cm)
Package 2 Width	39.37 in (100.0 cm)
Package 2 Length	47.24 in (120.0 cm)
Package 2 Weight	154.32 lb(US) (70.0 kg)

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Reach Regulation

[REACH Declaration](#)

Eu Rohs Directive

Pro-active compliance (Product out of EU RoHS legal scope)

China Rohs Regulation

[China RoHS declaration](#)

Product out of China RoHS scope. Substance declaration for your information.