Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Product data sheet

Specification





Plug-in bridge, Linergy TR, 4 points, for 2.5mm² terminal blocks, red, 4 way, set of 50

NSYTRAL24

Product availability: Stock - Normally stocked in distribution facility

Price*: 1.60 USD

Main

Range	Linergy
Product Name	Linergy TR
Product Or Component Type	Plug-in bridge
Device Short Name	TRA
Accessory / Separate Part Category	Connection accessory
Product Compatibility	TRV screw terminal terminal block TRP push-in terminal block TRR spring terminal terminal block TRH IDC terminal block
Number Of Ways	4 ways

Complementary

Cable Cross Section	0.00 in ² (2.5 mm ²)
Number Of Connections	4
	2
	3
Number Of Measurement Input	4
	2
	1
	6
	3
Quantity Per Set	Set of 50
Net Weight	0.12 oz (3.4 g)
Color	Red

Ordering and shipping details

Category	US10CP521715
Discount Schedule	0CP5
Gtin	3606480534072
Returnability	Yes
Country Of Origin	DE

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

0.98 in (2.500 cm)
2.36 in (6.000 cm)
5.91 in (15.000 cm)
0.11 oz (3.000 g)
BB1
50
0.98 in (2.500 cm)
2.36 in (6.000 cm)
5.91 in (15.000 cm)
6.00 oz (170.000 g)
S01
1250
5.91 in (15.000 cm)
5.91 in (15.000 cm)
15.75 in (40.000 cm)
9.67 lb(US) (4.386 kg)

Contractual warranty

Warranty 18 months



Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



RoHS/REACh

Well-being performance

⊘	Reach Free Of Svhc
⊘	Toxic Heavy Metal Free
⊘	Mercury Free
⊘	Rohs Exemption Information Yes
Ø	Halogen Free Plastic Parts Product

Certifications & Standards

Circularity Profile	No need of specific recycling operations
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Reach Regulation	REACh Declaration