Product data sheet

Specification





Screw bridge, Linergy TR, 2 pole, for NSYTRV162SF, set of 10

NSYTRALF1610

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 34.50 USD

Main

Range	Linergy	
Product Name	Linergy TR	
Product Or Component Type	Plug-in bridge	
Device Short Name	TRA	
Accessory / Separate Part Category	Connection accessory	
Product Compatibility	TRV screw terminal - fixed carrier terminal block	
Number Of Ways	10 ways	

Complementary

Cable Cross Section	0.02 in² (16 mm²)
Number Of Connections	10
Number Of Measurement Input	0

Ordering and shipping details

Category	US10CP521715	
Discount Schedule	0CP5	
Gtin	3606480616389	
Returnability	Yes	
Country Of Origin	US	

Packing Units

Unit Type Of Package 1	PCE	
Number Of Units In Package 1	1	
Package 1 Height	0.79 in (2.0 cm)	
Package 1 Width	4.72 in (12.0 cm)	
Package 1 Length	7.68 in (19.5 cm)	
Package 1 Weight	1.51 oz (42.9 g)	
Unit Type Of Package 2	BB1	
Number Of Units In Package 2	2 10	
Package 2 Height	0.79 in (2.0 cm)	
Package 2 Width	4.72 in (12.0 cm)	

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Package 2 Length	7.68 in (19.5 cm)	
Package 2 Weight	15.17 oz (430.0 g)	
Unit Type Of Package 3	S01	
Number Of Units In Package 3	200	
Package 3 Height	5.91 in (15.0 cm)	
Package 3 Width	5.91 in (15.0 cm)	
Package 3 Length	15.75 in (40.0 cm)	
Package 3 Weight	19.48 lb(US) (8.838 kg)	



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



RoHS/REACh

Well-being performance

②	Reach Free Of Svhc	
9	Toxic Heavy Metal Free	
②	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Circularity Profile	No need of specific recycling operations