Product data sheet

Specifications





Terminal block, Linergy TR, pushin type, 4 points, 4mm², protective earth, green-yellow, set of 50

NSYTRP44PE

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 8.00 USD

Main

Range	Linergy
Product Name	Linergy TR
Product Or Component Type	Terminal block
Device Short Name	TRP
Terminal Block Type	Protective earth
Terminal Block Level	1
Mounting Mode	Clip-on
Nominal Cross Section	0.01 in² (4 mm²)
Length	3.03 in (77 mm)
Color	Green-yellow
Quantity Per Set	Set of 50

Complementary

Width	0.24 in (6.2 mm)
Height	1.44 in (36.5 mm)
Connections - Terminals	2 x push-in downstream
	2 x push-in upstream
Number Of Connections	4
Connection Position	Тор
Number Of Measurement Input	2
Cable Cross Section	0.000.01 in² (0.086 mm²), solid
	0.000.01 in² (0.24 mm²), flexible with cable end
	0.000.01 in² (0.084 mm²), flexible without cable end
Wire Stripping Length	0.47 in (12 mm)
Tool Type	Disconnection flat screwdriver
	Connection without tool
Material	Polyamide 6/6: insulating case
Dielectric Loss	0.01 at 1 MHz IEC 60250
	0.01 at 1 MHz VDE 0303-T4
Dielectric Constant	3.7 at 1 MHz
Resistivity	10000 MΩ.m IEC 60093
	10000 MΩ.m VDE 0303-T30

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Surface Resistance	1000 GΩ IEC 60093 1000 GΩ VDE 0303-T30
Creep Resistance	500 CTI (> 400 kB) IEC 60093 500 CTI (> 400 kB) VDE 0303-T30
Flame Retardance	V0 0.03 in (0.8 mm) UL 94
Net Weight	0.61 oz (17.2 g)
Range Compatibility	Prisma G Prisma P Prisma PH Prisma Pack Spacial Kaedra Pragma TeSys
Product Compatibility	Spacial enclosures

Environment

Product Certifications	CSA LR
	EAC ATEX
	IEC-Ex
	GL cURus
Dielectric Strength	1000 V IEC 60243-1
Ambient Air Temperature For Operation	-40266 °F (-40130 °C) IEC 60216-1 -40266 °F (-40130 °C) VDE 0304-T21

Ordering and shipping details

Category	US10CP521715
Discount Schedule	0CP5
Gtin	3606480533341
Returnability	No
Country Of Origin	CN

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.97 in (5.0 cm)
Package 1 Width	2.76 in (7.0 cm)
Package 1 Length	10.63 in (27.0 cm)
Package 1 Weight	0.60 oz (17.0 g)
Unit Type Of Package 2	CAR
Number Of Units In Package 2	50
Package 2 Height	1.97 in (5.0 cm)
Package 2 Width	2.76 in (7.0 cm)
Package 2 Length	10.63 in (27.0 cm)
Package 2 Weight	32.06 oz (909.0 g)

Contractual warranty

Warranty

18 months



Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

⊘	Reach Free Of Svhc
⊘	Toxic Heavy Metal Free
⊘	Mercury Free
⊘	Rohs Exemption Information Yes
⊘	Halogen Free Plastic Parts Product

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations