



Vertical uprights height 1250mm. zinc-coated steel. Supply: 2 standard uprights.

NSYTVR125

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 157.80 USD

Main

Range	Thalassa
Accessory / Separate Part Category	Mounting accessory
Product Or Component Type	Technical upright
Device Application	Multi-purpose
Enclosure Nominal Dimensions	- H: 49.21 in (1250 mm)
Mounting Support	Direct fixing on the rear inserts Step slide
Range Compatibility	Thalassa Thalassa PLA
Device Composition	2 upright
Material	steel

Complementary

Surface Finish	Zinc coated
Fixing Mode	Bosses inserts M8 - rear of enclosure
Adjustment	Adjustable in depth every 25 mm with caged nuts Adjustable in height every 2.5 mm with quarter-turn nuts
Height	Nominal 49.21 in (1250 mm) Real 44.29 in (1125 mm)
Width	1.77 in (45 mm)
Depth	1.34 in (34 mm)
Thickness	0.08 in (2 mm)
Cut-Out Dimensions	11 x 13 mm

Ordering and shipping details

Category	US10ES180036
Discount Schedule	0ES1
Gtin	3606480185069
Returnability	No
Country Of Origin	FR

Packing Units

Unit Type Of Package 1	PCE
------------------------	-----

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Number Of Units In Package 1	1
Package 1 Height	1.38 in (3.5 cm)
Package 1 Width	2.36 in (6.0 cm)
Package 1 Length	44.49 in (113.0 cm)
Package 1 Weight	7.52 lb(US) (3.41 kg)
Unit Type Of Package 2	PAM
Number Of Units In Package 2	160
Package 2 Height	39.37 in (100.0 cm)
Package 2 Width	39.37 in (100.0 cm)
Package 2 Length	47.24 in (120.0 cm)
Package 2 Weight	1232.39 lb(US) (559.0 kg)

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

⊘	Reach Free Of Svhc	
9	Toxic Heavy Metal Free	
②	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations