## Product data sheet

Specifications





# Stainless canopy 304L, Scotch Brite® finish. for WM enclosure W600xD200mm

NSYTX6020

Product availability: Non-Stock - Not normally stocked in distribution facility

Price\*: 736.68 USD

#### Main

| Range                                 | Spacial                  |
|---------------------------------------|--------------------------|
| Accessory / Separate Part<br>Category | Enclosure accessory      |
| Product Or Component Type             | Canopy                   |
| Application                           | Multi-purpose            |
| Range Compatibility                   | Spacial Spacial S3X      |
| For Enclosure Nominal Dimensions      | -                        |
| Mounting Location                     | On top of enclosure      |
| Device Composition                    | 1 canopy fixing elements |

### Complementary

| Quantity Per Set | Set of 1               |
|------------------|------------------------|
| Material         | stainless steel 304L   |
| Surface Finish   | Scotch-Brite® brushed  |
| Fixing Mode      | By fixing element      |
| Height           | 2.76 in (70 mm)        |
| Width            | 23.82 in (605 mm)      |
| Depth            | 9.17 in (233 mm)       |
| Thickness        | 0.04 in (1 mm)         |
| Net Weight       | 4.38 lb(US) (1.988 kg) |

## Ordering and shipping details

| Category          | US10ES180036  |
|-------------------|---------------|
| Discount Schedule | 0ES1          |
| Gtin              | 3606480156243 |
| Returnability     | No            |
| Country Of Origin | BG            |

## **Packing Units**

| Unit Type Of Package 1       | PCE |
|------------------------------|-----|
| Number Of Units In Package 1 | 1   |

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

| Package 1 Height | 3.35 in (8.5 cm)       |
|------------------|------------------------|
| Package 1 Width  | 9.84 in (25.0 cm)      |
| Package 1 Length | 24.41 in (62.0 cm)     |
| Package 1 Weight | 4.38 lb(US) (1.988 kg) |

## **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

#### Well-being performance



Mercury Free



Rohs Exemption Information

Yes

#### **Certifications & Standards**

| Reach Regulation         | REACh Declaration  |
|--------------------------|--|
| Eu Rohs Directive        | Pro-active compliance (Product out of EU RoHS legal scope)   |
| China Rohs Regulation    | China RoHS declaration  Product out of China RoHS scope. Substance declaration for your information. |
| Environmental Disclosure | Product Environmental Profile  |
| Circularity Profile      | No need of specific recycling operations   |