



Price* : 1,354.81 USD



Main

Range	Spacial
Product name	Spacial VDM
Application	Electronic application
Product or component type	Compact enclosure
Body type	2-body
Rack type	Fixed
Enclosure nominal height	31.5 in (800 mm)
Enclosure nominal width	23.62 in (600 mm)
Enclosure nominal depth	14.96 in (380 mm)
Installation accessory type	Wall-mounting
Product destination	Electronics and networks
Device composition	1 1 1 inside the enclosure 2 top and bottom of rear 1 65 mm back from the front panel

Complementary

Door type	Glazed
Number of doors	1 front face
Door opening side	Reversible 120 °
Lock type	3 points lock, 3 mm double-bar
Type of gland plate	Standard
Number of units 19"	17
Accessibility for operation	Front body and front rear
Removable parts	Door by hinges Body by fixing element Rack
Material	Steel enclosure

	Galvanised steel 19" fixed rack
Surface finish	Epoxy-polyester powder enclosure
Colour	Grey RAL 7035 enclosure:
Standards	IEC 62208
Product weight	81.57 lb(US) (37 kg)

Environment

IP degree of protection	IP66 conforming to IEC 60529
IK degree of protection	IK08 conforming to IEC 62262

Ordering and shipping details

Category	80034 - ENCLOSURE SYSTEMS WALL MOUNT METAL
Discount Schedule	ES1
GTIN	003606480174643
Nbr. of units in pkg.	1
Package weight(Lbs)	81.400000000000006
Returnability	N
Country of origin	FR

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------