# **Product data sheet**

Specifications





① Discontinued

# Wall rack VDM 17U 2 bodies D380

NSYVD2M17U4

Discontinued on: Jun 30, 2023

Product availability: Non-Stock - Not normally stocked in distribution facility

### Main

Range	Spacial
Product Name	Spacial VDM
Application	Electronic application
Product Or Component Type	Compact enclosure
Body Type	2-body
Rack Type	Fixed
Enclosure Nominal Height	31.50 in (800 mm)
Enclosure Nominal Width	23.62 in (600 mm)
Enclosure Nominal Depth	14.96 in (380 mm)
Installation Accessory Type	Wall-mounting
Product Destination	Electronics and networks
Device Composition	1 rear part inside the enclosure 2 cable gland plate top and bottom of rear 1 19" fixed rack 65 mm back from the front panel 1 body 1 door with lock

## Complementary

Door Type	Glass
Number Of Doors	Front face 1
Door Opening Side	Reversible 120 °)
Lock Type	3 points lock, 3 mm double-bar
Type Of Gland Plate	Standard
Number Of Units 19"	17
Accessibility For Operation	Front body and front rear
Removable Parts	Door by hinges Body by fixing element Rack
Material	Enclosure steel 19" fixed rack galvanised steel
Surface Finish	Enclosure epoxy-polyester powder
Color	Enclosure Gray RAL 7035)
Standards	IEC 62208
Net Weight	81.57 lb(US) (37 kg)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Width	23.62 in (600 mm)
Height	31.50 in (800 mm)
Depth	14.96 in (380 mm)

## **Environment**

Ip Degree Of Protection	IP66 IEC 60529
Ik Degree Of Protection	IK08 IEC 62262

# Ordering and shipping details

Category	US10ES180034
Discount Schedule	0ES1
Gtin	3606480174643
Returnability	No
Country Of Origin	FR

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	33.07 in (84.0 cm)
Package 1 Width	24.41 in (62.0 cm)
Package 1 Length	16.93 in (43.0 cm)
Package 1 Weight	81.57 lb(US) (37.0 kg)

# **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

#### Well-being performance



Mercury Free



Rohs Exemption Information

Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration  Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile