

Product availability : Non-Stock - Not normally stocked in distribution facility



Price\*\* : 994.69 USD



### Main

Range	Spacial
Product name	Spacial VDM
Application	Electronic application
Product or component type	Compact enclosure
Body type	2-body
Rack type	Fixed
Enclosure nominal height	15.75 in (400 mm)
Enclosure nominal width	23.62 in (600 mm)
Enclosure nominal depth	14.96 in (380 mm)
Installation accessory type	Wall-mounting
Product destination	Electronics and networks
Device composition	1 rear part inside the enclosure 2 cable gland plate top and bottom of rear 1 19" fixed rack 65 mm back from the front panel 1 body 1 door with lock

### Complementary

Door type	Glazed
Number of doors	Front face 1
Door opening side	Reversible 120 °)
Lock type	3 mm double-bar lock
Type of gland plate	Standard
Number of units 19"	8
Accessibility for operation	Front body and front rear
Removable parts	Door by hinges Body by fixing element Rack
Material	Enclosure steel

	19" fixed rack galvanised steel
Surface finish	Enclosure epoxy-polyester powder
Color	Enclosure grey RAL 7035)
Standards	IEC 62208
Net weight	47.88 lb(US) (21.72 kg)

## Environment

IP degree of protection	IP66 IEC 60529
IK degree of protection	IK08 IEC 62262

## Ordering and shipping details

Category	80034 - ENCLOSURE SYSTEMS WALL MOUNT METAL
Discount Schedule	ES1
GTIN	03606480174612
Package weight(Lbs)	21.67 kg (47.78 lb(US))
Returnability	No
Country of origin	FR

## Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: No which is known to the State of California to cause No harm. For more information go to <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a>
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Not applicable, out of EU RoHS legal scope
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations

## Contractual warranty

Warranty	18 months
----------	-----------