# Product data sheet

Specifications

 Green Premium<sup>™</sup>



# Wall rack VDM 8U 2 bodies D480

NSYVD2M8U5

() Discontinued on: Jun 28, 2023

Product availability: Non-Stock - Not normally stocked in distribution facility

#### Main

Range	Spacial
Product Name	Spacial VDM
Application	Electronic application
Product Or Component Type	Compact enclosure
Body Type	2-body
Rack Type	Fixed
Enclosure Nominal Height	15.75 in (400 mm)
Enclosure Nominal Width	23.62 in (600 mm)
Enclosure Nominal Depth	18.90 in (480 mm)
Installation Accessory Type	Wall-mounting
Product Destination	Electronics and networks
Device Composition	1 rear part inside the enclosure 2 cable gland plate top and bottom of rear 1 19" fixed rack 65 mm back from the front panel 1 body 1 door with lock

#### Complementary

Glass
Front face 1
Reversible 120 °)
3 points lock, 3 mm double-bar
Standard
8
Front body and front rear
Door by hinges Body by fixing element Rack
Enclosure steel 19" fixed rack galvanised steel
Enclosure epoxy-polyester powder
Enclosure Gray RAL 7035)
IEC 62208
55.34 lb(US) (25.1 kg)

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Width	23.62 in (600 mm)
Height	15.75 in (400 mm)
Depth	18.90 in (480 mm)

## Environment

Ip Degree Of Protection	IP66 IEC 60529
Ik Degree Of Protection	IK08 IEC 62262

# Ordering and shipping details

Category	US10ES180034
Discount Schedule	0ES1
Gtin	3606480174667
Returnability	No
Country Of Origin	FR

## **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	16.54 in (42.0 cm)
Package 1 Width	20.28 in (51.5 cm)
Package 1 Length	24.02 in (61.0 cm)
Package 1 Weight	55.34 lb(US) (25.1 kg)
Unit Type Of Package 2	PAM
Number Of Units In Package 2	12
Package 2 Height	72.83 in (185.0 cm)
Package 2 Width	39.37 in (100.0 cm)
Package 2 Length	47.24 in (120.0 cm)
Package 2 Weight	692.69 lb(US) (314.2 kg)

## **Contractual warranty**

Warranty

18 months

# Sustainability Screen

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

#### Well-being performance

Mercury Free

Rohs Exemption Information Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile