Product data sheet

Specifications

Green Premium[™]



① Discontinued

Wall rack VDM 16U swi chass D400

NSYVDM16U4P

() Discontinued on: Sep 15, 2023

Product availability: Non-Stock - Not normally stocked in distribution facility

| Overview | |
|-----------------------------|--|
| Presentation | NEMA 12/IP66 rated assembled enclosure for OT, IT and networking applications. Form factor to easily install on the wall. Configurable to work as a ventilated enclosure with the addition of IP54 Climasys ventilation components. Ventilation system not included |
| Lead Time | Usually Ships within 4 Weeks |
| Main | |
| Range | Spacial |
| Product Name | Spacial VDM |
| Application | Electronic application |
| Product Or Component Type | Compact enclosure |
| Body Type | 1-body |
| Rack Type | Swing |
| Enclosure Nominal Height | 31.50 in (800 mm) |
| Enclosure Nominal Width | 23.62 in (600 mm) |
| Enclosure Nominal Depth | 9.84 in (250 mm) |
| Installation Accessory Type | Wall-mounting |
| Product Destination | Electronics and networks |
| Device Composition | 1 cable gland plate bottom 2 lock 19" swing rack 1 body 1 door with lock 1 19" swing rack |

Complementary

| Door Type | Glass |
|-----------------------------|--|
| Number Of Doors | Front face 1 |
| Door Opening Side | Reversible 120 °) |
| Lock Type | 3 points lock, 3 mm double-bar |
| Type Of Gland Plate | Standard |
| Number Of Units 19" | 16 |
| Accessibility For Operation | Front |
| Removable Parts | Door by hinges Rack by fixing element |

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

| Material | Enclosure and 19" rack steel |
|----------------|---|
| Surface Finish | Enclosure and 19" rack epoxy-polyester powder |
| Color | Enclosure and 19" rack Gray RAL 7035) |
| Standards | IEC 62208 |
| Net Weight | 76.06 lb(US) (34.5 kg) |
| Width | 23.62 in (600 mm) |
| Height | 31.50 in (800 mm) |
| Depth | 9.84 in (250 mm) |

Environment

| Ip Degree Of Protection | IP66 IEC 60529 |
|-------------------------|----------------|
| Ik Degree Of Protection | IK08 IEC 62262 |

Ordering and shipping details

| Category | US10ES180034 |
|-------------------|---------------|
| Discount Schedule | 0ES1 |
| Gtin | 3606480174544 |
| Returnability | No |
| Country Of Origin | FR |

Packing Units

| Unit Type Of Package 1 | PCE |
|------------------------------|-------------------------|
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 37.40 in (95.0 cm) |
| Package 1 Width | 47.24 in (120.0 cm) |
| Package 1 Length | 31.50 in (80.0 cm) |
| Package 1 Weight | 130.07 lb(US) (59.0 kg) |

Contractual warranty

Warranty

18 months

Sustainability Screen

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Mercury Free

Rohs Exemption Information Yes

Certifications & Standards

| Reach Regulation | REACh Declaration |
|--------------------------|--|
| Eu Rohs Directive | Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration |
| China Rohs Regulation | China RoHS declaration Product out of China RoHS scope. Substance declaration for your information. |
| Environmental Disclosure | Product Environmental Profile |