# Product data sheet

Specifications





# Polyester glassreinf. plinth for encl. PLA(T)124 front opening IP44-IK10 RAL7035

NSYZA2124G

Product availability: Non-Stock - Not normally stocked in distribution facility

#### Price\*: 280.00 USD

Main	
Range	Thalassa
Accessory / Separate Part Category	Enclosure accessory
Product Or Component Type	Plinth
Application	Multi-purpose
Nominal Dimensions Of The Housing	-
Device Composition	fixing elements 2 front panel 2 side part
Range Compatibility	Thalassa Thalassa PLA

## Complementary

Fixing Mode	By screws - on side parts
Color	Plinth Gray RAL 7035)
Height	7.87 in (200 mm)
Width	48.98 in (1244 mm)
Depth	13.78 in (350 mm)

## Environment

Ip Degree Of Protection	IP44
Ik Degree Of Protection	IK10

## Ordering and shipping details

Category	US10ES180036
Discount Schedule	0ES1
Gtin	3606480777745
Returnability	No
Country Of Origin	ES

## **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Package 1 Height	6.30 in (16.0 cm)
Package 1 Width	8.46 in (21.5 cm)
Package 1 Length	50.39 in (128.0 cm)
Package 1 Weight	20.99 lb(US) (9.52 kg)
Unit Type Of Package 2	PAL
Number Of Units In Package 2	20
Package 2 Height	51.18 in (130 cm)
Package 2 Width	39.37 in (100 cm)
Package 2 Length	37.80 in (96 cm)
Package 2 Weight	451.95 lb(US) (205 kg)

# Sustainability Screen Premium

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

#### Well-being performance

Mercury Free

Rohs Exemption Information Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations