



P10TV2R has not been replaced. Please contact your customer care center for more information.

Overview

Model Name	APC BASIC SURGE 10 OUTLET W/TEL&2COAX 120V RETAIL
Includes	1.8 Meter Tel cable (2)
Standard Lead Time	Usually in Stock
Product Distribution	Canada

Output

Number of Outlets	10
Receptacle Style	NEMA 5-15R

Input

Nominal Input Voltage	120V
Input Frequency	50/60 Hz +/- 5 Hz (auto sensing)
Input Connections	NEMA 5-15P
Maximum Line Current per phase	15.0 A

Surge Protection and Filtering

Surge energy rating	420 Joules
EMI/RFI Noise rejection (100 kHz to 10 MHz)	50.0 dB
Peak Current Normal Mode	11 kA
Peak Current Common Mode	20.0 kA
Data Line Protection	Co-axial Video / Cable protection
Let Through Voltage Rating	330

Physical

Net Weight	1.57 lbs (0.71 kg)
Maximum Height	9.75 inches (248.0 mm)
Maximum Width	3.75 inches (96.0 mm)
Maximum Depth	1.25 inches (32.0 mm)
Shipping Weight	2.0 lbs (0.91 kg)
Shipping Height	15.75 inches (401.0 mm)

Shipping Width	11.25 inches (286.0 mm)
Shipping Depth	3.0 inches (77.0 mm)
SCC Codes	10731304187353
Color	Black

Environmental

Operating Environment	32 - 104 °F (0 - 40 °C)
Operating Relative Humidity	0 - 95 %
Operating Elevation	0-10000 feet (0-3000 meters)
Storage Temperature	5 - 113 °F (-15 - 45 °C)
Storage Relative Humidity	0 - 95 %
Storage Elevation	0-50000 feet (0-15000 meters)

Conformance

Approvals	CSA
Standard warranty	Lifetime
Equipment protection policy	Lifetime : \$25000
UL 1449 TVSS Rating	330