

P232-4

APC ProtectNet, Standalone Surge Protector for four (4) RS232 lines



P232-4 has not been replaced. Please contact your customer care center for more information.

Overview

Model Name	APC ProtectNet, Standalone Surge Protector for four (4) RS232 lines
Includes	User Manual
Standard Lead Time	Usually in Stock
Product Distribution	Afghanistan

Input

Input Connections	--
-------------------	----

Surge Protection and Filtering

Peak Current Normal Mode	0.2 kA
Peak Current Common Mode	0.15000000596046448 kA
NM Surge Response Time (ns)	1.0 NS
Data Lines Protected(multi-line only)	1-8
Let Through Voltage Rating	20

Physical

Net Weight	1.0 lbs (0.45 kg)
Maximum Height	1.7 inches (44.0 mm)
Maximum Width	3.4 inches (87.0 mm)
Maximum Depth	3.2 inches (82.0 mm)
Shipping Weight	1.0 lbs (0.45 kg)
Shipping Height	2.0 inches (51.0 mm)
Shipping Width	9.5 inches (242.0 mm)
Shipping Depth	6.5 inches (166.0 mm)
Master Carton Units	5.0
Master Carton Weight	5.5 lbs
SCC Codes	10731304002977
Color	Black

Environmental

Operating Environment	5 - 113 °F (-15 - 45 °C)
-----------------------	--------------------------

Operating Relative Humidity	0 - 95 %
Storage Temperature	5 - 113 °F (-15 - 45 °C)
Storage Relative Humidity	0 - 95 %

Conformance

Standard warranty	Lifetime
-------------------	----------
