



P6 has not been replaced. Please contact your customer care center for more information.

ⓘ Discontinued

Overview

Model Name	APC BASIC SURGE 6 OUTLET 120V
Includes	User Manual
Standard Lead Time	Usually in Stock
Product Distribution	Canada

Output

Number of Outlets	6
Receptacle Style	NEMA 5-15R

Input

Nominal Input Voltage	120V
Input Frequency	50/60 Hz +/- 5 Hz (auto sensing)
Input Connections	NEMA 5-15P
Maximum Line Current per phase	15.0 A
Cord Length	6 feet (1.83 meters)

Surge Protection and Filtering

Surge energy rating	320 Joules
EP Joule Rating	820 Joules
EMI/RFI Noise rejection (100 kHz to 10 MHz)	55.0 dB
Peak Current Normal Mode	13 kA
Peak Current Common Mode	20.0 kA
Data Line Protection	--
Data Lines Protected(multi-line only)	--
Let Through Voltage Rating	330

Physical

Net Weight	0.92 lbs (0.42 kg)
Maximum Height	1.4 inches (36.0 mm)
Maximum Width	2.21 inches (56.0 mm)

Maximum Depth	12.4 inches (315.0 mm)
Shipping Weight	1.22 lbs (0.57 kg)
Shipping Height	1.5 inches (39.0 mm)
Shipping Width	4.41 inches (112.0 mm)
Shipping Depth	14.0 inches (356.0 mm)
Master Carton Units	12.0
Master Carton Weight	13.2 lbs
SCC Codes	10731304 01430 7
Color	Beige
Units per Pallet	1092.0

Environmental

Operating Environment	32 - 104 °F (0 - 40 °C)
Operating Relative Humidity	0 - 95 %
Operating Elevation	0-10000 feet (0-3000 meters)
Storage Temperature	5 - 113 °F (-15 - 45 °C)
Storage Relative Humidity	0 - 95 %
Storage Elevation	0-50000 feet (0-15000 meters)

Conformance

Approvals	CSA
Standard warranty	Lifetime
Equipment protection policy	Lifetime : \$10000
UL 1449 TVSS Rating	330