



Overview

Model Name	APC Power-Saving Essential SurgeArrest, 7 Outlets, 120V
Includes	User Manual
Standard Lead Time	Usually in Stock
Product Distribution	Anguilla , Aruba , Bahamas , Barbados , Belize , Bermuda , Canada , Colombia , Costa Rica , Cuba , Dominican Republic , Ecuador , El Salvador , Guatemala , Guyana , Haiti , Honduras , Jamaica , Mexico , Netherlands Antilles , Nicaragua , Panama , Puerto Rico , Trinidad And Tobago , Turks And Caicos Islands , United States , Venezuela , VIRGIN ISLANDS (UNITED STATES)

Output

Number of Outlets	7
Receptacle Style	NEMA 5-15R

Input

Nominal Input Voltage	120V
Input Frequency	50/60 Hz
Input Connections	NEMA 5-15P
Cord Length	4 feet (1.22 meters)
Maximum Input Current	15 A

Surge Protection and Filtering

Surge energy rating	1080 Joules
Peak Current Common Mode	72.0 kA
NM Surge Response Time (ns)	1.0 NS
Let Through Voltage Rating	400

Physical

Net Weight	1.0 lbs (0.45 kg)
Maximum Height	15.25 inches (387.0 mm)
Maximum Width	2.8 inches (71.0 mm)
Maximum Depth	1.4 inches (36.0 mm)
Shipping Weight	1.75 lbs (0.8 kg)

Shipping Height	19.25 inches (489.0 mm)
Shipping Width	7.0 inches (178.0 mm)
Shipping Depth	1.63 inches (41.0 mm)
Master Carton Units	6.0
Master Carton Dimensions (Length x Width x Height)	13.84 x 10.37 x 21.3 inches
Master Carton Weight	6.15 kg
SCC Codes	1073130426924 0
Color	White
Units per Pallet	198.0

Environmental

Operating Environment	32 - 113 °F (0 - 45 °C)
Operating Relative Humidity	0 - 95 %
Operating Elevation	0-10000 feet (0-3000 meters)
Storage Temperature	23 - 113 °F (-5 - 45 °C)
Storage Relative Humidity	0 - 95 %
Storage Elevation	0-50000 feet (0-15000 meters)

Conformance

Approvals	ETL , UL 1449
Standard warranty	Lifetime
Equipment protection policy	Lifetime : \$50000
UL 1449 TVSS Rating	<400

Sustainable Offer Status

RoHS	Compliant
REACH	REACH: Contains No SVHCs