

Product availability : Non-Stock - Not normally stocked in distribution facility



Price* : 366.00 USD

PA21600RC has not been replaced. Please contact your customer care center for more information.



ⓘ Discontinued

Main

| | |
|---------------------------|------------------------------|
| Product name | Square D |
| Product or component type | Rating plug |
| Trip unit technology | Magnetic Thermal-magnetic |
| Circuit breaker type | PAF PHF |

Complementary

| | |
|---------------------------|----------------|
| Line Rated Current | 1600 A |
| Poles description | 2P |
| System Voltage | 600 V AC |
| Magnetic tripping current | 5000...10000 A |

Environment

| | |
|------------------------|-----------|
| Product certifications | CSA UL |
|------------------------|-----------|

Ordering and shipping details

| | |
|-----------------------|------------------------------------|
| Category | 00975 - PA/C/H BRKR+SW+RATING CLMN |
| Discount Schedule | DE2 |
| GTIN | 00785901361633 |
| Nbr. of units in pkg. | 1 |
| Package weight(Lbs) | 0.9000000000000002 |
| Returnability | N |
| Country of origin | US |

Offer Sustainability

| | |
|------------------------|-----------------------------|
| RoHS (date code: YYWW) | Will be compliant on 4Q2016 |
|------------------------|-----------------------------|

Feb 19, 2019

Will be compliant on 4Q2016

California proposition 65

WARNING: Cancer and Reproductive Harm - www.P65Warnings.ca.gov

Contractual warranty

Warranty period

18 months
