



Price\*\* : 366.00 USD



PA2600RC has not been replaced. Please contact your customer care center for more information.

ⓘ Discontinued

### Main

Product name	Square D
Product or component type	Rating plug
Trip unit technology	Thermal-magnetic Magnetic
Circuit breaker type	PHF PAF

### Complementary

Line Rated Current	600 A
Poles description	2P
[Ue] rated operational voltage	600 V AC
Magnetic tripping current	3200...9000 A

### Environment

Product certifications	CSA UL
------------------------	-----------

### Ordering and shipping details

Category	00975-PA/C/H BRKR+SW+RATING CLM
Discount Schedule	DE2
Package weight(Lbs)	16.00 oz (453.592 g)
Returnability	No
Country of origin	US

### Contractual warranty

Warranty	18 months
----------	-----------