

Product availability : Non-Stock - Not normally stocked in distribution facility



Price* : 552.00 USD



PA31200RC has not been replaced. Please contact your customer care center for more information.

ⓘ Discontinued

Main

Product name	Square D
Product or component type	Rating plug
Trip unit technology	Magnetic Thermal-magnetic
Circuit breaker type	PAF PHF

Complementary

Line Rated Current	1200 A
Poles description	3P
System Voltage	600 V AC
Magnetic tripping current	3500...9000 A

Environment

Product certifications	CSA UL
------------------------	-----------

Ordering and shipping details

Category	00975 - PA/C/H BRKR+SW+RATING CLMN
Discount Schedule	DE2
GTIN	00785901773481
Nbr. of units in pkg.	1
Package weight(Lbs)	1.1500000000000001
Returnability	N
Country of origin	US

Offer Sustainability

RoHS (date code: YYWW)	Will be compliant on 4Q2016
------------------------	-----------------------------

Feb 22, 2019

Will be compliant on 4Q2016

California proposition 65

WARNING: Cancer and Reproductive Harm - www.P65Warnings.ca.gov

Contractual warranty

Warranty period

18 months
