

Product availability : Non-Stock - Not normally stocked in distribution facility



Price** : 552.00 USD



PA3800RC has not been replaced. Please contact your customer care center for more information.

ⓘ Discontinued

Main

Product name	Square D
Product or component type	Rating plug
Trip unit technology	Thermal-magnetic Magnetic
Circuit breaker type	PAF PHF

Complementary

Line Rated Current	800 A
Poles description	3P
[Ue] rated operational voltage	600 V AC
Magnetic tripping current	3200...9000 A

Environment

Product certifications	CSA UL
------------------------	-----------

Ordering and shipping details

Category	00975 - PA/C/H BRKR+SW+RATING CLMN
Discount Schedule	DE2
GTIN	00785901773467
Package weight(Lbs)	0.52 kg (1.15 lb(US))
Returnability	No
Country of origin	US

Offer Sustainability

California proposition 65	WARNING: Cancer and Reproductive Harm - www.P65Warnings.ca.gov
---------------------------	--

EU RoHS Directive	Not applicable, out of EU RoHS legal scope
-------------------	--

Contractual warranty

Warranty	18 months
----------	-----------
