Specifications





portal axis PAS E - profile size 60x60mm - toothed belt - ball stroke 300mm

PAS42E0300

() Discontinued on: Sep 19, 2022



Main

Range Of Product	Lexium PAS E	
Product Or Component Type	Portal axis	
Product Specific Application	For 1 direction	
Load Position	On carriage	
Drive Type	Toothed belt	
Type Of Guide	Ball	

Complementary

Operating Position	Horizontal	
Typlical Payload	26.46 lb(US) (12 kg)	
Distance Per Revolution	6.10 in (155 mm)	
Operating Force	800 N for Fx	
	2810 N for Fy	
	2810 N for Fz	
Maximum Speed	6.56 ft/s (2 m/s)	
Maximum Acceleration	n Acceleration 49.21 ft/s ² (15 m/s ²)	
Max. Drive Torque	35.40 lbf.in (4 N.m)	
Max. Torque	<44.25 lbf.in (5 N.m) for Mx	
	<97.36 lbf.in (11 N.m) for My	
	<150.46 lbf.in (17 N.m) for Mz	
Stroke	11.81 in (300 mm)	
Product Weight	16.53 lb(US) (7.5 kg) at 0 stroke with carriage and motor	
	2.20 lb(US) (1 kg) of carriage	
	23.59 lb(US) (10.7 kg) total	
Repeat Accuracy	+/- 0.05 mm	
Profile Dimension	60 x 60 mm	
Service Life	30000 km	
ssociated Module PLE60 planetary gearbox 5:1 supplied) BMH0702P06A2A servo motor supplied) LXM32.D12N4 servo drive not supplied)		

Ordering and shipping details

Gtin

3606485236605

Packing Units

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Unit Type Of Package 1	PCE	
Number Of Units In Package 1	1	
Package 1 Height	6.50 in (16.5 cm)	
Package 1 Width	19.21 in (48.8 cm)	
Package 1 Length	32.13 in (81.6 cm)	
Package 1 Weight	23.66 lb(US) (10.73 kg)	

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance


Reach Free Of Svhc
Mercury Free
Rohs Exemption Information Yes
Pvc Free

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Dimensions Drawings

Size Characteristics



- (1) LP : total length of axis
- (2) LC : length of carriage
- $(3) \qquad X: Stroke, \, refer \, to \, product \, characteristics.$

Α	mm	80
	in.	3.15
в	mm	60
	in.	2.36
B1	mm	278
	in.	10.94
с	mm	15
	in.	0.59
E0	mm	33
	in.	1.30
E1	mm	33
	in.	1.30
LC	mm	206
	in.	8.11

PAS42E0300

LP	mm	= 190 + LC + X
	in.	= 7.48 + LC + X
м	mm	75
	in.	2.95
Ø	mm	M5 X 12
	in.	M5 X 0.47
Ø1	mm	8 ^{H7} X 2.1
	in.	8 ^{H7} X 0.08

Mounting and Clearance


Servo Motor Mounting

Standard servo motor mounting

Servo motor mounted on the left

Performance Curves

Axis Positioning Time as a Function of the Stroke



X: Stroke

Y: Positioning time

Technical Description

Forces and Torques Exerted on the Lexium PAS E Portal Axis

