

Product data sheet

Characteristics

PBCE4A100AST120B

PB Busway Straight Distribution, 10ft, 100A

Product availability : Non-Stock - Not normally stocked in distribution facility



Price* : 1,860.00 USD



Main

Product or component type	Straight length
Range of product	Powerbus

Complementary

Line Rated Current	100 A
Busbar Configuration	4A L1 + L2 + N + L3
Busbar Material	Silver plated copper busbar
Integral Ground	50 percent capacity integral ground bus
System Voltage	600 V AC
Phase	3 phases
Wiring Configuration	4-wire (100 percent neutral)
Length	10 ft
Enclosure material	Painted aluminium black
Number of openings	10 each side

Environment

IP degree of protection	IP40
-------------------------	------

Ordering and shipping details

Category	20171 - 100A & 225A BUSWAY LENGTHS & FITTINGS
Discount Schedule	PE8
Nbr. of units in pkg.	1
Package weight(Lbs)	32
Returnability	Y

Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 1351 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Nickel compounds, which is known to the State of California to cause cancer, and
----- Substance 2	Bisphenol A (BPA), which is known to the State of California to cause birth defects or other reproductive harm.
----- More information	For more information go to www.p65warnings.ca.gov