

PBCE4A225ST120RB has not been replaced. Please contact your customer care center for more information.



ⓘ Discontinued

Overview

Description	Totally enclosed bus bar conductors with finger-safe plug-in openings. Outlets directly above racks ensure flexibility when you need to move, add, or change a branch circuit. Spring-joint connectors simplify installation and reduce maintenance requirements. No special tools required for installation.
Model Name	PB Busway Straight Distribution, 10ft, 225A, 240V
Standard Lead Time	Usually Ships within 3 Weeks
Product Distribution	Canada

Output

Maximum Total Current Draw per Phase	225 A
--------------------------------------	-------

Input

Nominal Input Voltage	240V
Input Frequency	60 Hz

Physical

Net Weight	51.0 lbs (23.18 kg)
Maximum Height	6.94 inches (176.0 mm)
Maximum Width	120.0 inches (3048.0 mm)
Maximum Depth	3.47 inches (88.0 mm)
Shipping Weight	96.0 lbs (43.64 kg)
Shipping Height	3.8 inches (97.0 mm)
Shipping Width	126.0 inches (3200.0 mm)
Shipping Depth	7.7 inches (196.0 mm)
Color	Black

Environmental

Operating Environment	14 - 104 °F (-10 - 40 °C)
Operating Relative Humidity	0 - 95 %
Operating Elevation	0-10000 feet (0-3000 meters)
Storage Temperature	-22 - 158 °F (-30 - 70 °C)
Storage Relative Humidity	0 - 95 %

Storage Elevation	0-15000 feet (0-4500 meters)
-------------------	------------------------------

Conformance

Approvals	CSA
Standard warranty	1 year (parts only)
