

Product data sheet

Characteristics

PBCE5A225AST048B

BUSWAY PLUG-IN STRAIGHT LGTH 4FT 225A 600V 3PH4W 5A CONFIG

Product availability : Non-Stock - Not normally stocked in distribution facility



Price* : 2,456.00 USD



Main

Product or component type	Straight length
Range of product	Powerbus

Complementary

Line Rated Current	225 A
Busbar Configuration	5A L1 + IG + L2 + N + L3
Busbar Material	Silver plated copper busbar
Integral Ground	50 percent capacity integral ground bus
System Voltage	600 V AC
Phase	3 phases
Wiring Configuration	4-wire (isolated ground and 100 percent neutral)
Length	4 ft
Enclosure material	Painted aluminium black
Number of openings	3 each side

Environment

IP degree of protection	IP40
-------------------------	------

Ordering and shipping details

Category	20171 - 100A & 225A BUSWAY LENGTHS & FITTINGS
Discount Schedule	PE8
Nbr. of units in pkg.	1
Package weight(Lbs)	23.199999999999999
Returnability	N

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Nickel compounds, which is known to the State of California to cause cancer, and
----- Substance 2	Bisphenol A (BPA), which is known to the State of California to cause birth defects or other reproductive harm.
----- More information	For more information go to www.p65warnings.ca.gov