

Product data sheet

Characteristics

PBCF4A100ATBM1UB

BUSWAY TAP BOX 100A 208Y/120V 3PH4W 4A CONFIG WITH METER

Product availability : Non-Stock - Not normally stocked in distribution facility



Price* : 5,397.00 USD



Main

Product or component type	Tap box
Range of product	Powerbus
Options	Meter PM5350

Complementary

Line Rated Current	100 A
Busbar Configuration	4A L1 + L2 + N + L3
Busbar Material	Silver plated copper busbar
Integral Ground	50 percent capacity integral ground bus
System Voltage	208Y/120 V AC
Phase	3 phases
Wiring configuration	4-wire (100 percent neutral)
Wire Gauge	AWG 10...AWG 2/0 1 ground AWG 6...300 kcmil 1 phase and neutral
Enclosure material	Painted aluminium black
Cable entry	Bottom

Environment

IP degree of protection	IP40
-------------------------	------

Ordering and shipping details

Category	20171 - 100A & 225A BUSWAY LENGTHS & FITTINGS
Discount Schedule	PE8
Nbr. of units in pkg.	1
Package weight(Lbs)	30

Returnability	N
---------------	---

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Nickel compounds, which is known to the State of California to cause cancer, and
----- Substance 2	Bisphenol A (BPA), which is known to the State of California to cause birth defects or other reproductive harm.
----- More information	For more information go to www.p65warnings.ca.gov
