

Product data sheet

Characteristics

PBCF4B400ATBB

BUSWAY TAP BOX 400A 600V 3PH3W 4B CONFIG

Product availability : Non-Stock - Not normally stocked in distribution facility



Price* : 4,750.00 USD



Main

Product or component type	Tap box
Range of product	Powerbus

Complementary

Line Rated Current	400 A
Busbar Configuration	4B L1 + IG + L2 + L3
Busbar Material	Silver plated copper busbar
Integral Ground	50 percent capacity integral ground bus
System Voltage	600 V AC
Phase	3 phases
Wiring configuration	3-wire (isolated ground)
Wire Gauge	AWG 1...600 kcmil 2 phase and neutral AWG 10...AWG 2/0 2 ground
Enclosure material	Painted aluminium black

Environment

IP degree of protection	IP40
-------------------------	------

Ordering and shipping details

Category	20171 - 100A & 225A BUSWAY LENGTHS & FITTINGS
Discount Schedule	PE8
Nbr. of units in pkg.	1
Package weight(Lbs)	95
Returnability	N

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Nickel compounds, which is known to the State of California to cause cancer, and
----- Substance 2	Bisphenol A (BPA), which is known to the State of California to cause birth defects or other reproductive harm.
----- More information	For more information go to www.p65warnings.ca.gov