



Main

Product or component type	Plug-in unit
Range of product	Powerbus

Complementary

Line Rated Current	100 A
System Voltage	240/415 V AC
Busbar Configuration	4A L1 + L2 + N + L3
Phase	3 phases
Wiring configuration	4-wire (100 percent neutral)
Circuit Breaker Type	EDU Breaker, 30 A AMP, 2 pole Number of Breakers 1 breaker
Number of Receptacles	Meter PM5350
Cable length	3 ft drop cable
Connector type	L6-30

Environment

NEMA Enclosure Rating	NEMA 1
IP degree of protection	IP40

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications