



Main

| | |
|---------------------------|--------------|
| Product or component type | Plug-in unit |
| Range of product | Powerbus |

Complementary

| | |
|-----------------------|--|
| Line Rated Current | 100 A |
| System Voltage | 240/415 V AC |
| Busbar Configuration | 5A L1 + IG + L2 + N + L3 |
| Phase | 3 phases |
| Wiring configuration | 4-wire (isolated ground and 100 percent neutral) |
| Circuit Breaker Type | EDU Breaker, 20 A AMP, 1 pole Number of Breakers 1 breaker |
| Number of Receptacles | Meter PM5350 |
| Cable length | 6 ft drop cable |
| Connector type | L5-20 |

Environment

| | |
|-------------------------|--------|
| NEMA Enclosure Rating | NEMA 1 |
| IP degree of protection | IP40 |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications