



### Main

Product or component type	Plug-in unit
Range of product	Powerbus

### Complementary

Line Rated Current	100 A
[Ue] rated operational voltage	208Y/120 V AC
Busbar Configuration	5B L1 + N + L2 + N + L3
Number of Phases	3 phases
Wiring configuration	4-wire (200 percent neutral)
Circuit Breaker Type	EDU, 30 A, 1 1 breaker
Number of Receptacles	PM5350 meter
Cable length	Drop cable 0.91 m (3 ft)
Connector type	L5-30

### Environment

NEMA Enclosure Rating	NEMA 1
IP degree of protection	IP40

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications.