

Product data sheet

Specifications

Schneider Electric

SQUARE PCSP200D2IP54 Picture



Active harmonic filter 200 amp 208-240 VAC IP54 Enclosure

PCSP200D2IP54

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 163,812.00 USD

Main

Range Of Product	AccuSine
Product Name	AccuSine PCS+
Product Or Component Type	Active harmonic filter

Complementary

Network Type	3P
Network Configuration	3 or 4 wires
Network Rated Voltage	208...240 V AC
Input Frequency	50/60 Hz +/- 3 Hz auto sensing
Maximum Permissible Voltage	1.1 x Un
Neutral Correction	Not provided
Rms Output Current Rating	200 A
Reactive Power Rating	83.1 kvar 240 V AC 50/60 Hz
Operating Modes	Power factor correction Mains current balancing Harmonic cancellation
Installation Location	Indoor
Enclosure Mounting	Floor-standing
Protection Type	Circuit breaker protection
Disconnect Type	Door-interlocked with rotary handle
Interrupt Capacity	200 kA
Heat Dissipation	Rear plenum with forced ventilation for high heat flow
Electromagnetic Compatibility	Conducted EMC, class A EN 61000-6-4
Accessibility For Operation	Front
Location Of Connection	Top or bottom

Environment

Enclosure Degree Of Protection	IP54
Environmental Characteristic	Operating 3C2 IEC 60721-3-3 Operating 3S2 IEC 60721-3-3 Storage 3C3 IEC 60721-3-3 Storage 3S3 IEC 60721-3-3

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Operating Altitude	<= 3280.84 ft (1000 m) 1 % per 100 m
Ambient Air Temperature For Operation	32...104 °F (0...40 °C) 32...122 °F (0...50 °C) maximum with current derating of 2 % per °C
Relative Humidity	0...95 %
Pcba Protection	Conformal coated
Standards	CSA C22.2 No 14 UL 60947-1 UL 508 EN 60439-1 CSA C22.2 No 60947-1-07 EN 61000-6-4
Product Certifications	ABS RCM CE cULus
Ambient Air Temperature For Storage	-4...140 °F (-20...60 °C)
Net Weight	798.07 lb(US) (362 kg)
Height	82.68 in (2100 mm)
Width	35.43 in (900 mm)
Color	Light gray RAL 7035)
Depth	23.62 in (600 mm)

Ordering and shipping details

Category	US1DE2C00089
Discount Schedule	DE2C
Gtin	3606489905552
Returnability	No

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	91.77 in (233.1 cm)
Package 1 Width	47.01 in (119.4 cm)
Package 1 Length	47.01 in (119.4 cm)
Package 1 Weight	877.44 lb(US) (398.0 kg)

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

Toxic Heavy Metal Free

Mercury Free

Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	End of Life Information
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov