

PCSPCT190X5000

AccuSine+ auxiliary transformer - 5/5 - Isolation Transformer

Product availability : Non-Stock - Not normally stocked in distribution facility



Main

Range	AccuSine
Product or component type	Auxiliary transformer
Accessory / separate part category	Measurement accessory
Range compatibility	AccuSine PCS+ active harmonic filter AccuSine PFV+ electronic VAR controller
Secondary current	5 A

Complementary

Current transformer ratio	5/5
Electrical connection	Studs 2500 V
Input impedance	0.5 Ohm
Line Rated Current	5 A
Thermal factor	1.33 at θ 30 °C 1 at θ 55 °C
Network frequency	50...400 Hz
System Voltage	600 V AC at 50...400 Hz
[Uimp] rated impulse withstand voltage	10 kV (50 μ s)
Mounting mode	By screws
Mounting support	Plate
Width	114.3 mm base width 114.3 mm body
Height	124 mm body
Depth	119.1 mm base depth 55.6 mm body
Product weight	3.97 lb(US) (1.8 kg)

Environment

Product certifications	CSA
------------------------	-----

Ordering and shipping details

Category	00089 - ACTIVE FILTERS
Discount Schedule	DE2C
GTIN	003606480891397
Nbr. of units in pkg.	1
Package weight(Lbs)	6.6100000000000003
Returnability	N
Country of origin	US
