

Product availability : Non-Stock - Not normally stocked in distribution facility



Main

Range	AccuSine
Product or component type	Current transformer
Accessory / separate part category	Measurement accessory
Range compatibility	AccuSine PCS+ active harmonic filter AccuSine PFV+ electronic VAR controller
Current transformer type	A type closed toroid
Secondary current	1 A

Complementary

Current transformer ratio	300/1
Electrical connection	Flying lead 609.6 mm AWG 16 600 V
Input impedance	5 Ohm
Line Rated Current	300 A
Network frequency	50...400 Hz
Measurement accuracy	1 %
Accuracy class	Class 1
System Voltage	600 V AC at 50...400 Hz
[Uimp] rated impulse withstand voltage	10 kV (50 μ s)
Depth	1.1 in (28 mm)
Diameter	Inner : 63.5 mm Outer : 116.3 mm
Product weight	1.5 lb(US) (0.68 kg)

Environment

Standards	UL 1015
Product certifications	CSA cURus

Ordering and shipping details

Category	00089 - ACTIVE FILTERS
Discount Schedule	DE2C
GTIN	003606480891526
Nbr. of units in pkg.	1
Package weight(Lbs)	2.2000000000000002
Returnability	N
Country of origin	US