



Overview

Model Name	3-Pole Circuit Breaker, 125A, T3 Type for Symmetra PX250/500kW
Includes	Installation guide
Standard Lead Time	Special Order - Call for Quoted Lead Times
Product Distribution	Albania

Output

Nominal Output Voltage	400 3PH
Maximum Total Current Draw per Phase	125 A
Output Connections	(1) Hard Wire 3-wire (3PH) (Battery Backup)

Input

Nominal Input Voltage	400 3PH
Input Frequency	50 Hz
Maximum Line Current per phase	125 A

Physical

Net Weight	6.1 lbs (2.77 kg)
Maximum Height	17.0 inches (432.0 mm)
Maximum Width	22.0 inches (559.0 mm)
Maximum Depth	21.5 inches (546.0 mm)
Shipping Weight	8.14 lbs (3.7 kg)
Shipping Height	17.0 inches (432.0 mm)
Shipping Width	22.0 inches (559.0 mm)
Shipping Depth	21.5 inches (546.0 mm)

Environmental

Operating Environment	32 - 104 °F (0 - 40 °C)
Storage Temperature	5 - 104 °F (-15 - 40 °C)

Conformance

Approvals	CE
Standard warranty	1 year repair or replace

Sustainable Offer Status

RoHS	Compliant
------	-----------
