



### Overview

Description	Designed to increase flexibility and agility of data center power distribution through a design that does not require a raised floor.
Model Name	InfraStruxure PDU 60kW 208V/208V
Includes	Installation guide
Standard Lead Time	Usually Ships within 3 Weeks
Product Distribution	Anguilla

### Output

Nominal Output Voltage	120V
Maximum Total Current Draw per Phase	167 A

### Input

Nominal Input Voltage	208 3PH
Input Frequency	60 Hz +/- 3 Hz
Number of Power Cords	1
Maximum Line Current per phase	167 A

### Physical

Net Weight	1012.0 lbs (460.0 kg)
Maximum Height	81.0 inches (2057.0 mm)
Maximum Width	24.0 inches (610.0 mm)
Maximum Depth	35.98 inches (914.0 mm)
Shipping Weight	1034.0 lbs (470.0 kg)
Shipping Height	86.0 inches (2184.0 mm)
Shipping Width	36.0 inches (914.0 mm)
Shipping Depth	48.0 inches (1219.0 mm)
Color	Black

### Environmental

Operating Environment	32 - 104 °F (0 - 40 °C)
-----------------------	-------------------------

Operating Relative Humidity	0 - 95 %
Operating Elevation	0-3333 feet (0-999.9 meters)
Storage Temperature	5 - 113 °F (-15 - 45 °C)
Storage Relative Humidity	0 - 95 %
Storage Elevation	0-30000 feet (0-9000 meters)

**Conformance**

Approvals	UL 60950
Standard warranty	1 year repair or replace