



Overview

Model Name	APC Workshop SurgeArrest 7 Outlets
Includes	User Manual
Product Distribution	Anguilla

Output

Number of Outlets	7
Receptacle Style	NEMA 5-15R

Input

Nominal Input Voltage	120V
Input Frequency	50/60 Hz +/- 5 Hz (auto sensing)
Input Connections	NEMA 5-15P
Maximum Line Current per phase	15.0 A
Cord Length	8 feet (2.44 meters)

Surge Protection and Filtering

Surge energy rating	800 Joules
EP Joule Rating	820 Joules
EMI/RFI Noise rejection (100 kHz to 10 MHz)	20.0 dB
Peak Current Normal Mode	6 kA
Peak Current Common Mode	12.0 kA
Let Through Voltage Rating	330

Physical

Net Weight	1.56 lbs (0.72 kg)
Maximum Height	14.96 inches (380.0 mm)
Maximum Width	2.76 inches (70.0 mm)
Maximum Depth	1.78 inches (45.0 mm)
Shipping Weight	1.11 lbs (0.5 kg)

Shipping Height	14.96 inches (380.0 mm)
Shipping Width	4.3 inches (109.0 mm)
Shipping Depth	2.0 inches (51.0 mm)
Master Carton Units	12.0
Master Carton Dimensions (Length x Width x Height)	31 x 13 x 6 inches
Master Carton Weight	10.1 kg
SCC Codes	1073130423832 1
Color	Yellow
Units per Pallet	180.0

Environmental

Operating Environment	32 - 104 °F (0 - 40 °C)
Operating Relative Humidity	0 - 95 %
Operating Elevation	0-10000 feet (0-3000 meters)
Storage Temperature	5 - 113 °F (-15 - 45 °C)
Storage Relative Humidity	0 - 95 %
Storage Elevation	0-50000 feet (0-15000 meters)

Conformance

Approvals	CSA
Standard warranty	Lifetime
Equipment protection policy	Lifetime : \$5000
UL 1449 TVSS Rating	330