



Overview

| | |
|----------------------|--|
| Description | Factory assembled and tested Power Distribution Modules include circuit breaker, power cord, power connection, and circuit monitoring. Auto-detection of modules by the Modular PDU minimizes installation time. |
| Model Name | APC IT Power Distribution Module 3x1 Pole 3 Wire 20A 250V L5-20 UL 680cm 860cm 1040cm |
| Includes | Installation guide |
| Standard Lead Time | Usually Ships within 3 Weeks |
| Product Distribution | Canada , Japan , United States |

Output

| | |
|--------------------------------------|----------------------------------|
| Nominal Output Voltage | 120V |
| Maximum Total Current Draw per Phase | 20 A |
| Output Connections | (3) NEMA L5-20R (Battery Backup) |

Input

| | |
|--------------------------------|---------|
| Nominal Input Voltage | 208 3PH |
| Input Frequency | 60 Hz |
| Maximum Line Current per phase | 20 A |

Physical

| | |
|-----------------|------------------------|
| Net Weight | 3.5 lbs (1.59 kg) |
| Maximum Height | 5.0 inches (127.0 mm) |
| Maximum Width | 17.5 inches (445.0 mm) |
| Maximum Depth | 16.0 inches (406.0 mm) |
| Shipping Weight | 5.5 lbs (2.5 kg) |
| Shipping Height | 5.0 inches (127.0 mm) |
| Shipping Width | 17.5 inches (445.0 mm) |
| Shipping Depth | 16.0 inches (406.0 mm) |
| Color | Black |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Conformance

| | |
|-------------------|--------------------------|
| Approvals | UL Listed |
| Standard warranty | 1 year repair or replace |

Sustainable Offer Status

| | |
|------|-----------|
| RoHS | Compliant |
|------|-----------|
