



Overview

Description	Factory assembled and tested Power Distribution Modules include circuit breaker, power cord, power connection, and circuit monitoring. Auto-detection of modules by the Modular PDU minimizes installation time.
Model Name	APC IT Power Distribution Module 2 Pole 3 Wire 30A L3-L1 L6-30 980CM
Includes	Installation guide
Standard Lead Time	Usually Ships within 3 Weeks
Product Distribution	Canada

Output

Nominal Output Voltage	208V
Maximum Total Current Draw per Phase	30 A
Output Connections	(1) NEMA L6-30R (Battery Backup)

Input

Nominal Input Voltage	208V
Input Frequency	60 Hz
Maximum Line Current per phase	30 A

Physical

Net Weight	9.44 lbs (4.29 kg)
Maximum Height	5.0 inches (127.0 mm)
Maximum Width	17.5 inches (444.0 mm)
Maximum Depth	16.0 inches (406.0 mm)
Shipping Weight	11.44 lbs (5.2 kg)
Shipping Height	5.0 inches (127.0 mm)
Shipping Width	17.5 inches (444.0 mm)
Shipping Depth	16.0 inches (406.0 mm)
Color	Black

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Environmental

Operating Environment	32 - 86 °F (0 - 30 °C)
Operating Relative Humidity	0 - 95 %
Operating Elevation	0-10000 feet (0-3000 meters)
Storage Temperature	5 - 104 °F (-15 - 40 °C)
Storage Relative Humidity	0 - 95 %
Storage Elevation	0-15000 feet (0-4500 meters)

Conformance

Approvals	UL Listed
Standard warranty	1 year repair or replace

Sustainable Offer Status

RoHS	Compliant
REACH	REACH: Contains No SVHCs